

Product Information

# Dynasylan® MEMO

## 3-methacryloxypropyltrimethoxysilane

### CAS NUMBER

2530-85-0

### PRODUCT DESCRIPTION

Dynasylan® MEMO is a methacrylfunctional silane that can be used as adhesion promoter, surface modifier, co-monomer for polymer synthesis and crosslinker.

Dynasylan® MEMO is a clear, colorless liquid. It is soluble in alcohols, and aliphatic or aromatic hydrocarbons.

#### Typical Properties

Property	Unit	Value
<b>Appearance</b>		colourless to yellowish liquid
<b>Boiling Point</b> (1013 hPa) DIN 51356	°C	≤255
<b>Chemical Name</b>		3-Methacryloxypropyltrimethoxysilane
<b>Density</b> (20 °C) OECD 109	g/cm <sup>3</sup>	1.05
<b>Flash Point</b> DIN EN ISO 2719	°C	≤110
<b>Refractive Index</b> (20,D) DIN 51423		1.432
<b>Viscosity</b> ( 20 °C) DIN 53015	mPa·s	2.8

The data represents typical values (no product specification)

### TYPICAL APPLICATIONS

Dynasylan® MEMO is used as adhesion promoter in applications such as:

- a constituent of glass fiber sizes (glass fiber fillers for unsaturated polyester resins and polyolefins)
- a finish for glass fabrics used in unsaturated polyester resins
- as a surface modifier for pigments and fillers for thermosets (unsaturated polyester, MMA), thermoplastics (polyesters and polyolefins) and elastomers
- as an additive for filled, peroxide-crosslinked elastomers
- as an additive for casting resins (unsaturated polyester, MMA)

Dynasylan® MEMO is either applied to the inorganic substrate as a pretreatment by dipping, spraying, or coating or it may be added directly to the resin matrix (additive process). For pretreatment, the silane may be used

- neat
- dissolved in an organic solvent
- dissolved in a mixture of organic solvent and water for partial hydrolysis
- completely hydrolyzed in aqueous solution.

To prepare an aqueous pretreatment solution, approx. 1-5 wt.% Dynasylan® MEMO is dissolved in water that has been adjusted to pH 3-4 with acetic acid. The solution will turn clear when the silane has fully hydrolyzed. The clear solution of Dynasylan® MEMO hydrolysate must be used within 1-2 days, if it turns cloudy again it may no longer be used. In the additive process, Dynasylan® MEMO is mixed with the resin or polymer before or together with the filler. A prerequisite for this method is compatibility of the silane with the resin since the silane must not react prematurely with the resin.

## BENEFITS & ADVANTAGES

When used correctly Dynasylan® MEMO can achieve the following properties, for example in a highly-filled unsaturated resin system:

- optimum dispersion of the fillers/pigments
- reduction in settling of the fillers/pigments
- a reduction in viscosity and improved flow properties of the resin
- improved mechanical properties of the molded products
- improved resistance of the molded products to boiling water, acids and alkalis

Dynasylan® MEMO can be used as monomer during resin synthesis (e.g. latex dispersions). It may partially replace the methacryl-functional monomers (usually 0.5-3%, but sometimes up to 20%). The thus incorporated silane functionality can lead to improved properties in the final application (e.g. coating or sealant) of such resins:

- wet adhesion strength
- chemical resistance
- mar resistance

## HANDLING & PROCESSING

The alkoxy group of Dynasylan® MEMO hydrolyzes in the presence of water (and a suitable catalyst such as acetic acid) to produce methanol and reactive silanol (Si-OH) groups which can bond to a variety of inorganic substrates. The methacryl groups interacts with the polymer. Examples of suitable inorganic substrates are glass, glass fibers, glass wool, mineral wool, silicic acid, quartz, sand, cristobalite, wollastonite and mica; also suitable are aluminium hydroxide, kaolin, talc, other silicate fillers, metal oxides and metals.

Examples of suitable polymers include unsaturated polyester, acrylates and vinyl esters.

Before considering the use of Dynasylan® products please read its Safety Data Sheet (SDS) thoroughly for safety and

toxicological data as well as for information on proper transportation, storage and use.

The Safety Data Sheet is available on our website <https://silanes.evonik.com/en> or upon request from your local representative, customer service or from Evonik Operations GmbH, Product Safety Department, E-MAIL [sds-hu@evonik.com](mailto:sds-hu@evonik.com).

## PACKAGING

Dynasylan® MEMO is supplied in 25 kg, 215 kg drums and 1.000 kg IBC bulk containers.

## SHELF LIFE

In the unopened container Dynasylan® MEMO has a shelf life of min. 12 months from delivery.

### Registration Listings

Registry	Status
Australia (AIIC)	Yes
Canada (DSL)	Yes
China (IECSC)	Yes
EU (EINECS/ELINCS)	Yes
EU (REACH)	Yes
Japan (ENCS)	Yes
South Korea (KECL)	Yes
Philippines (PICCS)	Yes
USA (TSCA)	Yes

### Disclaimer

This information and all further technical advice are based on our present knowledge and experience. However, it implies no liability or other legal responsibility on our part, including with regard to existing third-party intellectual property rights, especially patent rights. In particular, no warranty, whether express or implied, or guarantee of product properties in the legal sense is intended or implied. We reserve the right to make any changes according to technological progress or further developments. The customer is not released from the obligation to conduct careful inspection and testing of incoming goods. Performance of the product described herein should be verified by testing, which should be carried out only by qualified experts in the sole responsibility of a customer. Reference to trade names used by other companies is neither a recommendation, nor does it imply that similar products could not be used.

### Evonik Operations GmbH

Smart Effects  
Rodenbacher Chaussee 4  
63457 Hanau  
Germany  
[ask-se@evonik.com](mailto:ask-se@evonik.com)  
[ask-se-asia@evonik.com](mailto:ask-se-asia@evonik.com)  
[ask-se-america@evonik.com](mailto:ask-se-america@evonik.com)  
[www.evonik.com/smarteffects](http://www.evonik.com/smarteffects)